




Pass and Seymour  
Hospital Grade 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Red  
Part No. 1597HGRED



Hospital-Grade 15A Self-Test Duplex GFCI

## Features & Benefits

Hospital Grade Self-Test GFCI

## Specifications

### General Info

|                   |                                     |                       |                         |
|-------------------|-------------------------------------|-----------------------|-------------------------|
| Product Line      | Pass & Seymour                      | Color                 | Red                     |
| Country Of Origin | China                               | Number of Receptacles | 2                       |
| Outlet Type       | Commercial, GFCI, Indoor, Self-Test | Application Sector    | Residential/Commercial  |
| Standard          | cULus, UL Listed, FSUL              | Warranty Type         | 1-Year Limited Warranty |
| Type              | Outlet                              |                       |                         |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

|                          |                        |                  |                    |
|--------------------------|------------------------|------------------|--------------------|
| Interrupt Rating         | 4 A                    | Frequency Rating | 60 Hz              |
| Trip Range               | 5±1 mA                 | Connection       | Back and Side Wire |
| Amperage                 | 15 A                   | Number of Poles  | Double Pole        |
| Indoor/Outdoor           | Indoor                 | Voltage          | 125.0 V            |
| Environmental Conditions | 95% Humidity, UL 94 V2 |                  |                    |

---