



Pass and Seymour
SteriGuard™ Antimicrobial Straight Blade Connector 20A, 125V, Yellow
Part No. 15W33AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

| | |
|--|---|
| UL and CSA Listed | NSF (National Sanitation Foundation) Certified |
| Patent Pending | Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi |
| Anti-microbial Additive Resistant to Scuffing and Cleaning | Escherichia (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99% |
| Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97% | Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97% |
| RoHS Compliant (Non-Halogenated) | Independently tested and Certified to JIS Z2801 standards |
| Resistant to High Pressure Hose-down applications | Tongue & Groove Environmental Sealing |
| Keyed Body and Cover for Alignment | NEMA Type 4, 4x, 6, 6P and IP67 Protection |
| Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care. | |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Application Sector | Commercial |

| | | | |
|-----------------------|-----------------------------|--------------------------|---|
| Standard | CSA Listed, FSUL, UL Listed | | |
| Dimensions | | | |
| Product Height US | 1.85 in | Product Length US | 4.03 in |
| Technical Information | | | |
| Phase | Single | Connection | Cable |
| Number of Wires | 3 | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 18 - 12 AWG |
| Voltage | 125.0 V | Environmental Conditions | Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized |