



Pass and Seymour
Discontinued - 20A, 125V Turnlok® Ground Continuity Monitoring (GCM) Plug
Part No. 27W47GCM



Rated watertight for 1,500 psi high-pressure hosedown, P&S watertight GCM plugs and connectors feature multiple seals to ensure protection against the environment. The transparent body houses dual LED lights with 360° visibility, indicating ground continuity and power status, while providing a NEMA 6P/IP67 rating.

Features & Benefits

Integral indication of ground continuity and power status. Convenient continuous monitoring enhances personnel safety.

Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.

Recessed cord-grip screw reduces screwdriver slippage for improved safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.

Color-coded terminal screws are positioned on the same plane and backed-out for fast installation.

For covering patents, see www.legrand.us/patents.

Dual, bright LED indicators with 360 degree visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross. For 250V configurations: Hot to ground cross will be indicated by a green and red LED.

Exclusive two-piece cord grip accepts a wide range of cord widths and provides more consistent pressure for superior conductor retention.

Internal dust shield keeps terminals free of contaminants.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized		
