

TVSS Specification Grade Quad Receptacle, 20A 125V



## Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Mexico	Application Sector	Residential/Commercial

Standard  
UL1449, UL498: ANSI/IEEE C62.41  
(Formerly IEEE 587), ANSI/IEEE C62.45  
Installation Categories "A" (Ring Wave)  
"B" (Unidirectional Impulse).

### Technical Information

Number of Wires	3	Temperature Rating	-40° - 65° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Voltage	125.0 V

---

Environmental Conditions Flammability: UL94 V2 and UL94-5 VA

---