



Pass and Seymour  
20A 250V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Ivory  
Part No. 5862I

Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 250V



## Features & Benefits

|   |  |
|---|--|
| Heavy-duty, brass strap for added strength and ground conductivity.   | Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.   |
| Strap tabs wrap around face to prevent strap from separating from face and back body.   | Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.  |
| High strength nylon face.   | Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.  |
| Auto-ground clip assures positive ground.   | For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .   |
| For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> . | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.<br>Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

## Specifications

### General Info

|                   |                               |                       |            |
|-------------------|-------------------------------|-----------------------|------------|
| Product Line      | Pass & Seymour                | Color                 | Ivory      |
| Country Of Origin | Mexico                        | Number of Receptacles | 2          |
| Outlet Type       | Commercial, Indoor            | Application Sector    | Commercial |
| Standard          | cULus UL498, CSA C22.2 No. 42 | Type                  | Outlet     |

### Dimensions

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

---

Product Height US 2.635 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber 140596 cULus Listed Yes

---

### Technical Information

---

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

---

Number of Wires 3 Temperature Rating -40° - 60° C

---

Amperage 20 A Number of Poles Double Pole

---

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

---

Voltage 250.0 V Environmental Conditions Flammability: UL94 V2

---