



For deep switches and receptacles. Base has two 1/2" trade size KO's. Larger gang boxes available by special order. Two-gang: 4 3/4" L x 4 3/4" W (121mm x 121mm). Accepts NEMA double-gang standard faceplates. NOTE: Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "VC" or the "WH" color suffix to "WHC" to denote the Canadian versions.

## Features & Benefits

For deep switches and receptacles. Base has two 1/2" trade size KO's. Larger gang boxes available by special order. Two-gang: 4 3/4" L x 4 3/4" W (121mm x 121mm). Accepts NEMA double-gang standard faceplates. NOTE: Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "VC" or the "WH" color suffix to "WHC" to denote the Canadian versions.

## Specifications

### General Info

|                   |  |                    |                        |
|-------------------|--|--------------------|------------------------|
| Product Line      | Wiremold   | UPC Number         | 786776562996           |
| Country Of Origin | United States  | Application Sector | Residential/Commercial |
| Standard          | cULus Listed Raceway: File E4376 Guide RJBT.<br>Fittings: File E4751 Guide RJPR. Meets Article 386 of NEC. Meets Section 12-1600 of CEC. | Type               | Raceway                |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 4.75 in | Product Depth US | 1.75 in |
| Product Length US | 4.75 in |                  |         |

### Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

### Additional Information

|                 |     |                               |     |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

### Technical Information

|         |         |
|---------|---------|
| Voltage | 600.0 V |
|---------|---------|