




radiant Collection
radiant® Tamper-Resistant Outlet, Black
Part No. 885TRBK



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Indoor, Residential, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

Voltage	125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)
---------	---------	--------------------------	---