



adorne Collection  
**Discontinued - adorne® sofTap Wi-Fi Ready Scene Controller, Magnesium**  
Part No. ADTPRIWHCM1



Create and enjoy up to four customized lighting scenes with this addition to adorne's Wi-Fi Lighting solutions. Get perfect lighting at the tap of a button with four presets. Pair with the adorne Hub to create a smart Wi-Fi Lighting Control solution for your home. Turn lights on/off, or dim them, with just the lightest tap of a finger, or create custom lighting scenes in the Legrand Lighting Control app for smartphones and tablets. Also compatible with the Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428431510	Country Of Origin	China
Application Sector	Residential	Standard	UL, FCC, cULus, RoHS

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

---

Technical Information

---

Requires Neutral Wire	Yes	Connection Type	Internal Pressure Plates
-----------------------	-----	-----------------	--------------------------

---