



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. 5862RED



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 250V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

Number of Wires 3 Temperature Rating -40° - 60° C

Amperage 20 A Number of Poles Double Pole

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

Voltage 250.0 V Environmental Conditions Flammability: UL94 V2
