



Wiremold
20GB506TRUSB 5' Plugmold® Multioutlet System with USB
Part No. BK20GB506TRUSB

5' Plugmold Multioutlet USB system



Features & Benefits

USB charging. 2.4A USB type A receptacle charges faster than other USB receptacles and is compatible with USB 2.0 and 3.0 type devices.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

This product meets the material restrictions of RoHS.

Tamper-resistant receptacles. Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.

Compact design. Eliminates the need for bulky AC adapters.

Specifications

General Info

| | | | |
|--------------------|---------------|-----------------------|--|
| Product Line | Wiremold | UPC Number | 786776182545 |
| Country Of Origin | United States | Number of Receptacles | 9 |
| Application Sector | Commercial | Standard | cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC. |
| Type | Plugmold | | |

Dimensions

| | | | |
|------------------|--------|------------------|---------|
| Product Width US | 1.3 in | Product Depth US | 0.75 in |
|------------------|--------|------------------|---------|

| | |
|-------------------|--------|
| Product Length US | 1.3 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|--------------------------|------------------------|----------|---------|
| Frequency Rating | 60 Hz | Amperage | 20 A |
| Enclosure Type | Steel | Voltage | 125.0 V |
| Environmental Conditions | Dry interior locations | | |