



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

Features & Benefits

Part of an acclAIM Connectivity Solution: Typical total channel loss of 0.4 dB

Bend-insensitive fiber for optimal cable management and ease of installation

TIA Channel Compliant

Dust caps pre-installed

Specifications

General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	United States		

Dimensions

Product Weight US	0.04 lb	Product Length US	1.0 m
-------------------	---------	-------------------	-------

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	acclAIM/UPC
Jacket Application	Plenum Rated	Minimum Insertion Loss	55 dB
Number of Fanout Cables	4	Jacket Rating	Plenum OFNP-Rated
Fanout Cable Diameter	2 mm	Connector Type	Infinium acclAIM
Fanout Cable Length	24 in	Wavelength	1310 nm, 1550 nm
Operating Temperature	32°-158°F	Fiber Size	9/125
Maximum Insertion Loss	0.3 dB	Storage Temperature	-40° - 158° F