




Ortronics
10 Meters (10 m), 4 Duplex LC/UPC To acclAIM/UPC, 9/125 OS2 Single-Mode, ONFP Plenum, 8 Fiber, Distribution Harness Cable, Yellow
Part No. C80AM137S5JEM0010M



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

Features & Benefits

Part of an acclAIM Connectivity Solution: Typical total channel loss of 0.4 dB

Bend-insensitive fiber for optimal cable management and ease of installation

TIA Channel Compliant

Dust caps pre-installed

Specifications

General Info

Product Line Ortronics Color Yellow

Country Of Origin United States

Dimensions

Product Weight US 0.39 lb Product Length US 10.0 in

Technical Information

Fiber Optic Cable Type OS2 Jacket Application Plenum Rated

Minimum Insertion Loss 55 dB Number of Fanout Cables 4

Jacket Rating Riser OFNR-Rated Fanout Cable Diameter 2 mm

Fanout Cable Length 24 in Wavelength 1310 nm, 1550 nm

Operating Temperature 32°-158°F Fiber Size 9/125

Maximum Insertion Loss 0.3 dB