



Pass and Seymour  
DR Series CFL/LED/Incandescent Single Pole/3-Way Rotary Dimmer, Preset, Black  
Part No. DRCL453PBK



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

Convenient Operation - Combines ON/OFF Decorator style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products Higher ratings

Single pole and 3-way operation

Screw-pressure-plate back wire terminals to save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Features	Locator Light
Switch Type	Push, Rotary	Number of Switches	1
Warranty Type	Limited Lifetime Warranty		

### Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.19 in		

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Amperage	4.5 A	Bulb Compatibility	CFL, Incandescent, LED
----------	-------	--------------------	------------------------

---

Number of Poles	3-Way, Single Pole	Wattage	700 W
-----------------	--------------------	---------	-------

---

Voltage	120.0 V
---------	---------

---