



Pass and Seymour
Commercial Specification Grade 15A 125V Duplex Receptacle, White
Part No. CRI5WCC12

- Commercial grade corrosion-resistant, plated-steel outlet strap built for heavy-duty use.

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly	.032 inch thick, brass, triple-wipe power contacts for lasting retention
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring	Impact-resistant nylon face and thermoplastic back body
Accepts 14 to 10 AWG solid or stranded copper or copper-clad wire	Terminal compartments isolated from each other for positive conductor containment
Tri-drive terminal and mounting screws	Auto-ground clip assures positive ground
Posted, ready-to-wire terminal screws for added productivity	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Receptacle Type	Double
Number of Receptacles	2	Construction	Nylon face with impact-resistant thermoplastic back body
Outlet Type	Commercial	Application Sector	Commercial
Standard	UL, CSA	Type	Corrosion Resistant, Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125.0 V
Connection Type	Wired	Environmental Conditions	90% (relative humidity, non-condensing)
