



FC22: Bus Drop, Closed Mesh, Single Eye, Cable Diameter 0.22 - 0.32 inches, Bale Length 9-in, Mesh Length 3.5-in, Break Strength 1100 lbs.



## Features & Benefits

Bus drop grips are used as cable support. They relieve any direct tension from the critical connection and absorb vibration and flexing.

Bus drop grips are woven of galvanized steel wire.

They are offered with either the single eye or locking bale attachment.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 9: Mesh Length: 3.5

## Specifications

### General Info

|              |   |                    |            |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour  | Country Of Origin  | Mexico     |
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard     | UL/CSA Approval (consult factory)                         |                    |            |

### Dimensions

|                  |         |                   |        |
|------------------|---------|-------------------|--------|
| Product Width US | 0.32 in | Product Length US | 3.5 in |
|------------------|---------|-------------------|--------|

### Listing Agencies / 3rd Party Agencies

|            |     |                 |       |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

### Technical Information

|                     |                               |                     |  |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 0.22 in                       | Minimum Cable Range | 0.32 in  |
| Capacity            | Various Cable Diameter Ranges | Mounting            | Consult the Factory for Mounting Recommendations |
| Load                | Approx. Break Strength: 1100  |                     |  |