




Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



Features & Benefits

Unique Key and Color Options: Up to thirteen unique keying options/colors for a wide range of network security systems, easy identification and network management.

Keyed front or Rear: Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirements. Internal keying feature prevents tampering

Various Footprint Options: Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility.

Compatibility: All Legrand keyed LC fiber products are engineered to be compatible with other Legrand products to provide an end to end, data center to desktop solution.

Specifications

General Info

| | | | |
|-------------------|-----------|------------|---|
| Product Line | Ortronics | UPC Number | 662875027614 |
| Country Of Origin | Mexico | Standard | RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 4.19 in | Product Depth US | 0.66 in |
| Product Height US | 1.24 in | | |

Technical Information

| | | | |
|--------------|------------------------------------|-----------------------|-----------|
| Adapter Rear | Keyed | Adapter Front | Keyed |
| Form Factor | LC Duplex | Operating Temperature | -40°-75°C |
| Durability | < 0.2dB typical change,500 matings | | |