



Pass and Seymour

15A 125V Heavy Duty Spec-Grade Isolated Ground Decorator Duplex Receptacle, Back and Side Wire, White

Part No. IG26262W



Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Face color coding by voltage facilitates locating and mating of proper devices.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2