



Isolated Ground Quad Receptacle 20A 125V Orange

## Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                   |                         |                    |                        |
|-------------------|-------------------------|--------------------|------------------------|
| Product Line      | Pass & Seymour          | Color              | Orange                 |
| Country Of Origin | Mexico                  | Application Sector | Residential/Commercial |
| Standard          | UL498, CSA C22.2 No. 42 |                    |                        |

### Listing Agencies / 3rd Party Agencies

|            |     |                 |       |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 16063 |
|------------|-----|-----------------|-------|

### Technical Information

|                 |   |                    |              |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 65° C |
|-----------------|---|--------------------|--------------|

|                          |                                     |                 |             |
|--------------------------|-------------------------------------|-----------------|-------------|
| Amperage                 | 20 A                                | Number of Poles | Double Pole |
| Wire Size                | 14 - 12 AWG                         | Voltage         | 125.0 V     |
| Environmental Conditions | Flammability: UL94 V2 and UL94-5 VA |                 |             |