



Turnlok® Receptacle Single 3-Wire 20A 125V Isolated Ground



Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A).	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.	1 filtering capacitor for 7 to 1 average noise reduction.
Nominal let-through (suppressed) voltage in all 3 modes, 500V.	LED indicator light.
Overcurrent protection in all 3 modes.	Electronic components potted for electrical, mechanical and thermal stability.
Thermal protection in all 3 modes.	Back and side wire capability including ground terminal.
Operating temperature: -40: C to 85: C (-40: F to 185: F)	Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Industrial	Standard	UL 498
Type	Outlet		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Wire Size	18 - 0 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		