

Turnlok® Single Receptacle 3-Wire 15A 277V Isolated Ground



## Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability. Accepts #14-#10 AWG.

## Specifications

### General Info

|                    |                 |                       |           |
|--------------------|-----------------|-----------------------|-----------|
| Product Line       | Pass & Seymour  | Color                 | Orange    |
| Finish             | Matte           | Country Of Origin     | Mexico    |
| Receptacle Type    | Locking         | Number of Receptacles | 1         |
| Application Sector | Industrial      | Standard              | UL Listed |
| Type               | Isolated Ground |                       |           |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.437 in | Product Depth US | 4.03 in |
| Product Height US | 1.203 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                         |       |                 |             |
|-------------------------|-------|-----------------|-------------|
| CSA Listed              | Yes   | cULus Listed    | Yes         |
| CSA File Number         | 16063 |                 |             |
| Technical Information   |       |                 |             |
| Phase                   | 3     | Number of Wires | 3           |
| Amperage                | 15 A  | Number of Poles | Double Pole |
| NEMA Configuration Code | L7-15 | Voltage         | 277.0 V     |