



**Wattstopper**  
**DLM Segment Network Wire, 4000 Spool**  
Part No. LM-MSTP-S4000



This type of wire connects low voltage devices (i.e., switches, occupancy sensors, photocells) to panels. It is #20 AWG wire that meets UL and NEC standards for Class 2 applications. Plenum rated wire meets plenum and riser requirements. Several types of multi-conductor low voltage wires are available for standard, pilot, locator, and multilevel switching or for connecting photocells to the LI control panels. This wire can also be used to wire relays remotely

## Features & Benefits

Data communications wire provides communications between panels and signaling devices

Custom cut to specified lengths

Distance markings in foot increments

Low voltage component wire connects switches, sensors, and other low voltage devices to panels

Color-coded for streamlined installation

## Specifications

### General Info

Product Line	Wattstopper	Color	Green
UPC Number	754182938254	Country Of Origin	United States
Product Series	LM-MSTP	Jacket Color	Light Green
Application Sector	Commercial	Standard	UL, cUL
Warranty Type	5-Year	Type	Cable, Spool

### Dimensions

Product Width US	15.5 in	Product Weight US	82.0 lb
Product Volume US	3123.3 cu in	Product Depth US	15.5 in
Product Height US	13.0 in	Cable Length	4000 ft

---

## Technical Information

---

Wire Gauge	22 AWG	Jacket Application	Plenum Rated
Shielded/Unshielded Cable	Shielded	Conductor	1.5-Pair
Protocol	MS/TP	Jacket Rating	CL3P Rated, CMP Rated, FT6 Rated
Temperature Rating	75° C	Cable Diameter	0.185 mm
Indoor/Outdoor	Indoor		

---