



**Wattstopper**  
**Low Voltage Wall Switch, 1-Button w/LED, Black**  
Part No. LVSW-101-B



LVSW-100 Series Low Voltage Switches are lighting control devices that use conventional point-to-point low voltage wiring for control of single or multiple loads. Each button provides a momentary contact that is intended for use with compatible low voltage relay panels or similar lighting control panels or devices. Each button has an LED indicator that can serve as a status indicator or as a locator light.

## Features & Benefits

- Sleek single gang devices fit decorator wall plates (not supplied); 1-, 2-, 3-, 4-, and 8-button models
- Blue LED indicator on each button can be used as a locator light or as a status indicator
- Five color options and custom engraving options; standard buttons may be replaced in the field
- The product meets the materials restrictions of RoHS

## Specifications

### General Info

|                  |              |                   |        |
|------------------|--------------|-------------------|--------|
| Product Line     | Wattstopper  | Color             | Black  |
| UPC Number       | 754182931347 | Country Of Origin | China  |
| Package Quantity | 1            | Type              | Switch |

### Dimensions

|                   |             |                   |         |
|-------------------|-------------|-------------------|---------|
| Product Width US  | 2.0 in      | Product Weight US | 0.22 lb |
| Product Volume US | 22.52 cu in | Product Depth US  | 2.24 in |
| Product Height US | 4.49 in     |                   |         |

### Additional Information

|                 |     |  |     |
|-----------------|-----|--|-----|
| RoHS Conformant | Yes | DesignLights Consortium Qualified System | Yes |
| Security        | Yes |  |     |

### Technical Information

|                 |        |                   |        |
|-----------------|--------|-------------------|--------|
| Number of Gangs | 1      | Number of Buttons | 1      |
| Amperage        | 2 mA   | Indoor/Outdoor    | Indoor |
| Voltage         | 24.0 V |                   |        |