



Multi-Weave, Flexible Eye. Cable Diameter - 3.500-3.990-inch, Mesh Length - 56-inch, Eye Diameter - 5/8-inch, Breal Strength - 48,000 lbs, Light Green.

Features & Benefits

Multi-weave pulling grips are constructed of high strength galvanized steel and are designed for pulling aluminum or copper bare conductor, wire rope and insulated cables.

Multi-weave pulling grips are available with a flexible and rotating eye, which can be attached to a swivel.

The rotating eye can turn to relieve pulling torque when tension is relaxed.

These grips are used in applications such as distribution line stringing and overhead transmission.

Description : Rotating Eye: The forged steel rotating eye will thread through sheaves and blocks without binding, but is not a swivel and will not turn under tension.

Mesh Length: 56: Eye Diamater: 5/8

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations

Load

Approx. Break Strength: 48000 (Lt
Green)
