



Pass and Seymour
60A 3 Pole 4 Wire Fusible Mechanical Interlock
Part No. PS460FMIR7W



Triple pole, Four wire, Fusible Mechanical Interlock Receptacle. 6 amp, 480 vac.

Features & Benefits

| | |
|---|---|
| Top or Bottom feed. | Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout. |
| End user decides at installation whether top or bottom feed is appropriate. | No closure plug kits required. |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | United States | Application Sector | Industrial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 9.13 in | Product Depth US | 9.94 in |
| Product Height US | 24.5 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|----------|---------|-----------------|-------|
| Phase | 3 | Number of Wires | 4 |
| Amperage | 60 A | Number of Poles | 3-Way |
| Voltage | 480.0 V | | |