



Pass and Seymour
Non-Fusible Safety Switch, 60A
Part No. PS60SS



Non-Fusible Safety Switch, 60 Amps, 600 VAC. The first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as Suitable as Motor Disconnect per NEC Article 430.109(A)(6). Pass and Seymour Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions.

Features & Benefits

Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.

Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.

Durable, stainless steel coverretaining chain makes installation and maintenance more convenient.

Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle.

Bottom and top wiring access options. No unnecessary openings to compromise water resistance.

Certified for IP69 applications.

Nonconductive, watertight, corrosion-, heat-, and impact-resistant thermoplastic enclosure ensures NEMA 4X and 12 ratings. Withstands the harshest industrial environments.

Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting without special brackets or harnesses.

Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout provisions and provides plenty of grip for sure, easy operation.

Switch entry into the enclosure is offset to the side and sealed to provide enhanced water resistance.

Top mount auxiliary contact enables additional control functions or signal lights.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|---------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007150100 |
| Country Of Origin | United States | Application Sector | Industrial |
| Standard | UL 498 | Type | Safety Switch |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 9.13 in | Product Depth US | 6.31 in |
| Product Height US | 12.38 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 31169 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Technical Information

| | | | |
|---------------------------|---|-----------------|---------------------------|
| Horsepower Rating | 10 HP @ 208 VAC, 10 HP @ 240 VAC, 15 HP @ 277 VAC, 20 HP @ 3ø 240 VAC, 20 HP @ 3ø 480 VAC, 20 HP @ 3ø 600 VAC, 20 HP @ 3øY 120/208 VAC, 20 HP @ 480 VAC, 3 HP @ 120 VAC, 40 HP @ 3øY 277/480 VAC, 50 HP @ 3øY 347/600 VAC | Connection | Hardwired |
| Amperage | 60 A | Enclosure Type | NEMA 12, NEMA 4X, Plastic |
| Number of Poles | 3-Way | Wire Size | #14 - #10 AWG |
| Maximum Horsepower Rating | 50 HP @ 3øY 347/600 VAC | Wiring Location | Bottom, Top |
| Voltage | 120 to 600 V | | |