



## Legrand Non-Fusible Safety Switch, 60 Amps Part No. PS60SS



Non-Fusible Safety Switch, 60 Amps, 600 VAC. The first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as Suitable as Motor Disconnect per NEC Article 430.109(A)(6). P&S Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions.

### Features & Benefits

|   |   |
|---|---|
| Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage. | Nonconductive, watertight, corrosion-, heat-, and impact-resistant thermoplastic enclosure ensures NEMA 4X and 12 ratings. Withstands the harshest industrial environments. |
| Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.   | Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting without special brackets or harnesses.  |
| Durable, stainless steel coverretaining chain makes installation and maintenance more convenient.                           | Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout provisions and provides plenty of grip for sure, easy operation.  |
| Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle. | Switch entry into the enclosure is offset to the side and sealed to provide enhanced water resistance.  |
| Bottom and top wiring access options. No unnecessary openings to compromise water resistance.                               | Top mount auxiliary contact enables additional control functions or signal lights.  |
| Certified for IP69 applications.  |   |

### Specifications

#### General Info

|                     |                |
|---------------------|----------------|
| Color               | Gray           |
| UPC Number          | 785007150100   |
| Countries Of Origin | United States  |
| Product Line        | Pass & Seymour |
| Application Sector  | Industrial     |
| Standard            | UL 498         |

#### Listing Agencies / 3rd Party Agencies

|                     |       |
|---------------------|-------|
| cULus Listed        | Yes   |
| cULus ListingNumber | 31169 |

#### Technical Information

---

|                        |       |
|------------------------|-------|
| <b>Number of Poles</b> | 3-Way |
|------------------------|-------|

---

|                |       |
|----------------|-------|
| <b>Voltage</b> | 600 V |
|----------------|-------|

---