



Pass and Seymour
Non-Fusible Mechanical Interlock
Part No. PS430MIR9W



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock Receptacle.
30A, 3, 240V.

Features & Benefits

| | |
|---|---|
| Top or Bottom feed. | Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout. |
| End user decides at installation whether top or bottom feed is appropriate. | No closure plug kits required. |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 6.88 in | Product Depth US | 8.25 in |
| Product Height US | 12.38 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 31169 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Technical Information

| | | | |
|-----------|-------|-----------------|---------|
| Phase | 3 | Number of Wires | 4 |
| Amperage | 30 A | Number of Poles | 3-Way |
| Wire Size | 2 AWG | Voltage | 250.0 V |