



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS460MIR12W



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock Receptacle.  
60A, 120/240V.

Features & Benefits

|   |   |
|---|---|
| Top or Bottom feed.   | Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout. |
| End user decides at installation whether top or bottom feed is appropriate. | No closure plug kits required.  |

Specifications

General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | United States  | Application Sector | Industrial |
| Standard          | UL Listed      |                    |            |

Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 6.88 in | Product Depth US | 9.0 in |
| Product Height US | 9.0 in  |                  |        |

Technical Information

|          |         |                 |       |
|----------|---------|-----------------|-------|
| Phase    | 3       | Number of Wires | 4     |
| Amperage | 60 A    | Number of Poles | 3-Way |
| Voltage  | 125.0 V |                 |       |