



Straight Blade Connector 2-Pole 3-Wire 20A 125A

## Features & Benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly. Nylon housing provides impact and chemical resistance. Rugged two-piece cord grip provides more uniform cord retention. Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors. All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity. Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |          |        |
|-------------------|----------------|----------|--------|
| Product Line      | Pass & Seymour | Color    | Black  |
| Country Of Origin | Mexico         | Standard | UL 498 |
| Type              | Straight Blade |          |        |

### Dimensions

|                  |          |                   |          |
|------------------|----------|-------------------|----------|
| Product Width US | 1.516 in | Product Length US | 2.638 in |
|------------------|----------|-------------------|----------|

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

### Technical Information

---

|            |                |                 |             |
|------------|----------------|-----------------|-------------|
| Connection | Wire Grounding | Number of Wires | 3           |
| Amperage   | 20 A           | Number of Poles | Double Pole |
| Wire Size  | 4              | Voltage         | 125.0 V     |

---