



The PW-301 passive infrared (PIR) wall switch sensor can turn lights OFF and ON based on occupancy.

Features & Benefits

Color-matched lens and low profile for appealing design

120/240/277 VAC and 347 VAC models

High sensitivity and dense coverage for exceptional performance

Optional neutral connection with break off tab to expose neutral terminals

Allows multi-way control from one of up to four control locations

Defaults to Manual-ON operation for maximum energy savings

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
Application Sector	Commercial		

Dimensions

Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in

Technical Information

Response Frequency	60 Hz	Sensor Type	Occupancy
Number of Buttons	1	Indoor/Outdoor	Indoor
Wattage	1200 W	Mounting Type	Box
Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
Connection Type	Wired	Load	1000W