



The PW-302 passive infrared (PIR) wall switch sensor turns lights ON and OFF based on occupancy.

Features & Benefits

Defaults to Auto-ON to 50% operation for maximum energy savings

120/240/277 VAC and 347 VAC models

High sensitivity and dense coverage for exceptional performance

Optional neutral connection with break off tab to expose neutral terminals

Allows multi-way control from one of up to four control locations

Two relays for control of two separate lighting loads or circuits

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
Application Sector	Commercial		

Dimensions

Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in

Technical Information

Response Frequency	60 Hz	Sensor Type	Occupancy
Number of Buttons	2	Indoor/Outdoor	Indoor
Wattage	1200 W	Mounting Type	Box
Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
Connection Type	Wired	Load	800W