



Pass and Seymour
PlugTail® Connector, Right Angle Stranded, 6-in XHHW-2 Wire
Part No. PTR6STRX2



PlugTail® Connectors, Right Angle, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Ideal for application with low leakage current requirements. Utilizes XHHW-2 wire.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

Wire temperature rated 90°C Wet/Dry.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Substantially higher insulation resistance than THHN wire.

Ideal for projects requesting that products be free of any components on Red List.

PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Gray	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
------------------	--------	-------------------	---------

Product Height US	1.0 in	Product Length US	6.0 in
-------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Connection Type	Plugtail, Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
-----------------	-----------------	--------------------------	--
