



**Wattstopper**  
**Discontinued - PIR Dimmable Wall Switch Sensor, 120/277V, Grey**  
Part No. PW-100D-G



The PW-100D and PW-101D passive infrared (PIR) dimmable wall switch sensors can turn light OFF and ON based on occupancy. It is characterized by high sensitivity to small and large movements, appealing aesthetics, and a variety of features.

## Features & Benefits

High sensitivity and dense coverage for exceptional performance

Defaults to Manual-ON operation for maximum energy savings

Color-matched lens and low profile for appealing design

Pushbutton dimming control and optional locked preset level for many lighting types

Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience

Part of a comprehensive line of PIR, Ultrasonic and Dual Technology wall switch sensors

Part of a comprehensive line of PIR, Ultrasonic and Dual Technology wall switch sensors

Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI

Vandal resistant lens combines precise coverage with durability

Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds

In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations

Selectable audible and/or visual alerts for impending shutoff

2-wire and 3-wire models available for applications with or without neutral wire

## Specifications

### General Info

Product Line	Wattstopper	Replaced by Part Number	PW-101D-G
Color	Gray	UPC Number	754182930821
Country Of Origin	China	Features	IR (Infrared), Motion Sensor

Switch Type	Motion Sensor	Application Sector	Commercial
Warranty Type	5-Year		
<b>Dimensions</b>			
Product Width US	2.0 in	Product Weight US	0.4 lb
Product Volume US	27.84 cu in	Product Depth US	4.5 in
Product Height US	2.25 in		
<b>Additional Information</b>			
Product Environmental Profile	Yes		
<b>Technical Information</b>			
Response Frequency	50/60 Hz	Sensor Type	Occupancy
Number of Buttons	1	Amperage	4.3 A
Indicator	LED Light	Wattage	1200 W
Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Voltage	120/277 V
Connection Type	Wired		