



radiant Collection
radiant® 15A 3-Way Switch, White, with Microban®
Part No. TM873WAMCC4



This switch features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

Allowing control of a light or fixture from two separately located switches, the radiant® 3-Way Switch with Microban upgrades your space with clean lines and smooth paddle action for a sophisticated touch.

Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

This product is not currently available for sale in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Uses a paddle switch for smoother control with a low-profile aesthetic.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate (also available with Microban), and coordinate with other designer switches and outlets available from the radiant® Collection.

Replaces any standard switch with ease, in as little as 10 minutes.

Allows you to control a light fixture from two locations in a room.

Designed to install easily with a narrower back body and captivated mounting screws.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Glossy	Country Of Origin	China
Features	Antimicrobial Protection	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential/Commercial
Standard	RoHS, CSA, UL, cULus	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

Product Height US	4.19 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Actuator	Paddle	Connection	Screw Terminals
----------	--------	------------	-----------------

Amperage	15 A	Number of Poles	3-Way
----------	------	-----------------	-------

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

Voltage	120/277 V	Environmental Conditions	0 to 90% (relative humidity, non-condensing)
---------	-----------	--------------------------	--
