



radiant Collection
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, Light Almond
Part No. RCD38TRLA



A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|-------------------------|--------------------|----------------------------|
| Product Line | Pass & Seymour | Color | Light Almond |
| Country Of Origin | China | Features | Combination, Locator Light |
| Switch Type | Push | Number of Switches | 1 |
| Application Sector | Residential | Standard | cULus, UL Listed |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet, Switch |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.29 in | Product Depth US | 1.59 in |
| Product Height US | 3.81 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|--------------------------|---------|-----------------------|--------------------|
| Is Tamper-Resistant | Yes | Contact Configuration | 15A |
| Operating Cycles | 50000 | Contact Rating | 125 |
| Number of Gangs | 1 | Number of Poles | 3-Way, Single Pole |
| Mounting Type | Box | Voltage | 125.0 V |
| Environmental Conditions | UL94 V2 | | |