



Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 15A, 125V



Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

AC receptacles available in 15 and 20A, 125V.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|-------------------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor, Tamper-Resistant |
| Application Sector | Commercial | Standard | UL 498 |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 1.13 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|-----|-------|-------|
| Is Tamper-Resistant | Yes | Phase | Three |
|---------------------|-----|-------|-------|

| | | | |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

| | | | |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
|----------------|--------|---------|---------|
